



Kommunikations-Element passt in den Isolierkörper der Winkeldose Serie 723 von Fa. Intercontec.

Bei JH kann unter ID1043027-xx die Winkelflanschdose inkl. Isolierkörper und Kontakten bestellt werden.

Temperatursensor / Temperature sensor	
Biegeradius min. / min. bend radius	3mm
Durchmesser / Diameter	2,0mm
Querschnitt / Cross section	0,16mm ² / AWG26

Biegeradius min. dauernd
Min. bend radius for flexing

--

Biegeradius min. einmalig
Min. bend radius for rigid configuration

10mm

Schleppkettenradius min.
Min. drag chain radius

--

max. Kabellänge (L): siehe Techn. Daten des Gerätetyps
For max. cable length (L): See Specifications of the encoder model

			IDnumber:
			Change No. N2094 Phase: Serie
	Original drawing Scale	Format	AGK JAE --> Kommunikations-Element (9SS0) Anschlussmaße
Dimensions in mm	1:1	A3	
			Tolerierung nach DIN ISO 8015 Tolerances as per DIN ISO 8015
			Allgemeintoleranzen ISO 2768-mH ±0,2mm; +0,2 General tolerances ISO 2768-mH ±0,2mm; +0,2
The reproduction, distribution and utilization of this document as well as the communication of its contents to others without express authorization is prohibited. Offenders will be held liable for the payment of damages. All rights reserved in the event of the grant of a patent, utility model or design. (ISO 16016)			
HEIDENHAIN DR. JOHANNES HEIDENHAIN GmbH 83301 Traunreut, Germany			Document number D 1063040-00-B-02
			1 of 1 Version Revision Sheet