



Kommunikations-Element passt in den Isolierkörper der Winkeldose Serie 723 von Fa. Intercontec.

Bei JH kann unter ID1043027-xx die Winkelanschdose inkl. Isolierkörper und Kontakten bestellt werden.

Biegeradius min. dauernd Min. bend radius for flexing	--
Biegeradius min. einmalig Min. bend radius for rigid configuration	10mm
Schleppkettenradius min. Min. drag chain radius	--

max. Kabellänge (L): siehe Techn. Daten des Gerätetyps
For max. cable length (L): See Specifications of the encoder model

		IDnumber:
		Change No. N2094 Phase: Serie
	Original drawing Scale Format	AGK JAE --> Kommunikations-Element (9SS0)
Dimensions in mm	1:1 A3	Anschlussmaße
		Tolerierung nach DIN ISO 8015 Tolerances as per DIN ISO 8015
		Allgemeintoleranzen ISO 2768-mH ±0.2 General tolerances ISO 2768-mH ±0.2
The reproduction, distribution and utilization of this document as well as the communication of its contents to others without express authorization is prohibited. Offenders will be held liable for the payment of damages. All rights reserved in the event of the grant of a patent, utility model or design. (ISO 16016)		
HEIDENHAIN DR. JOHANNES HEIDENHAIN GmbH 83301 Traunreut, Germany		Document number D 1063040-00-B-04
		1 of 1 Version Revision Sheet