



max. Kabellänge (L): siehe Techn. Daten des Gerätetyps

			IDnumber:
			Change No. C179342-5 Phase: Serie
	Original drawing	APK Hybrid-Stecker M23 Bu / Sub-D (2XS01)	
	Scale	Format	Tolerances as per ISO 8015
Dimensions in mm	1:1	A3	General Tolerances ISO 2768:1989-mH ±0,2
The reproduction, distribution and utilization of this document as well as the communication of its contents to others without express authorization is prohibited. Offenders will be held liable for the payment of damages. All rights reserved in the event of the grant of a patent, utility model or design. (ISO 16016)			
HEIDENHAIN		Released	Version Revision Sheet
DR. JOHANNES HEIDENHAIN GmbH 83301 Traunreut, Germany		10.12.2024	D 1064165 - 01 - C - 06
			1 of 1
			Document number