





XI	Anschluss-Belegung
	Elektrischer Anschluss
	Geometrie Polbild (Steckseite)
..	Ausgangssignal
..	Eingangssignal
DQ01	Datenschnittstelle
..	Teilkreiszusatzspur
15 polig	Kundenseitige Steckerausführung
14	Versorgung 0V (Un)
12	Versorgung +V (Up)
9	Serielle Schnittstelle TX+
10	Serielle Schnittstelle TX-
7	Serielle Schnittstelle RX+
8	Serielle Schnittstelle RX-
5	Zusätzliche Signale Temperatur +
6	Zusätzliche Signale Temperatur -
1	Freie Litzen und Pins
2	Freie Litzen und Pins
3	Freie Litzen und Pins
4	Freie Litzen und Pins
11	Freie Litzen und Pins
13	Freie Litzen und Pins
15	Freie Litzen und Pins
0060	Ergänzungen

0060 = Freie Litzen und Pins dürfen nicht belegt werden!

XI	Pin configuration
	Electrical connection
	Geometry of pole pattern (plug side)
..	Output signal
..	Input signal
DQ01	Data interface
..	Additional circular-scale track
15-pin	Customer's connection version
14	Supply 0V (Un)
12	Supply +V (Up)
9	Serial interface TX+
10	Serial interface TX-
7	Serial interface RX+
8	Serial interface RX-
5	Additional signals temperature +
6	Additional signals temperature -
1	Free wires and pins
2	Free wires and pins
3	Free wires and pins
4	Free wires and pins
11	Free wires and pins
13	Free wires and pins
15	Free wires and pins
0060	Additions

0060 = Vacant pins or wires must not be used!