



CZ = common zone
LE = line Element (ISO 1101:2008)

| | |
|---------------------------|------------|
| Abtastkopf / encoder head | 1166688-01 |
| Maßstab / scale | 1169550-01 |

| | | | | |
|------------------|--------|-----------------------------------|---------|---|
| Original drawing | | ERP1081 | ERP1081 | Tolerierung nach DIN ISO 8015 Tolerances as per DIN ISO 8015 |
| Scale | Format | | | |
| Dimensions in mm | 1:1 A3 | Anschlussmaße / Mating Dimensions | | Allgemeintol. ISO 2768-mH $\leq 6\text{mm}$: $\pm 0,2$ General tol. ISO 2768-mH $\leq 6\text{mm}$: $\pm 0,2$ |

The reproduction, distribution and utilization of this document as well as the communication of its contents to others without express authorization is prohibited. Offenders will be held liable for the payment of damages. All rights reserved in the event of the grant of a patent, utility model or design. (ISO 16016)