


| | | |
|---|--|-------------------|
| JA | Anschluss-Belegung | |
|  | Elektrischer Anschluss | |
| .. | Geometrie Polbild (Steckseite) | |
| JH | Firmenname | JH |
| .. | Ausgangssignal | .. |
| .. | Eingangssignal | .. |
| Pana01 | Datenschnittstelle | Pana01 |
| .. | Teilkreiszusatzspur | .. |
| 10 polig | Kundenseitige Steckerausführung | Ader |
| 2 | Versorgung 0V (Un) | weißgrün und weiß |
| 1 | Versorgung +V (Up) | braungrün+blau |
| Im Stecker | Versorgung verbunden mit Sensorleitung | Im Stecker |
| Gehäuse | Außenschirm | Schirm |
| 3 | Serielle Schnittstelle REQ/Serial Data + | violett |
| 4 | Serielle Schnittstelle REQ/Serial Data - | gelb |
| 5;6;7;8;9;10 | Freie Adern und Pins | |
| | Freie Adern und Pins | grau |
| | Freie Adern und Pins | rosa |

| | | |
|---|---|------------------------|
| JA | Pin configuration | |
|  | Electrical connection | |
| .. | Geometry of pole pattern (plug side) | |
| JH | company name | JH |
| .. | Output signal | .. |
| .. | Input signal | .. |
| Pana01 | Data interface | Pana01 |
| .. | Additional circular scale track | .. |
| 10-pin | Customer's connection version | Wire |
| 2 | Supply 0V (Un) | white, green and white |
| 1 | Supply +V (Up) | brown, green and blue |
| in connector | Supply connected with sensor line | in connector |
| Housing | External shield | Shield |
| 3 | Serial interface REQ/Serial Data + | violet |
| 4 | Serial interface REQ/Serial Data - | yellow |
| 5;6;7;8;9;10 | Free wires and pins | |
| | Free wires and pins | grey |
| | Free wires and pins | pink |

| | | | | | | | |
|---|--|--|--|-------------------------------|---------|-----------------------|-------|
| Connection layout JA DIB10 .. Pana01 JH | | | | Pin Layout | | Change No: C043455-05 | |
| The reproduction, distribution and utilization of this document as well as the communication of its contents to others without express authorization is prohibited. | | | | | | | |
| HEIDENHAIN DR. JOHANNES HEIDENHAIN GmbH | | | | Serie | Version | Revision | Sheet |
| | | | | D1177297 - 01 - A - 01 | | Page 1/1 | |
| | | | | Document No | | | |