



- H1 Taststiftaufnahme M3
Stylus holder M3
- H2 Auswechselbare Taststifte nach Typenübersicht D295695
Exchangeable styli as per table of types D295695
- Überlauf mit T404: Z: 5 mm; X/Y 5 mm
Overtravel with T404: Z .197"; X/Y .197"
- H3 Montagesockel mit axialem Kabelausgang
Mounting socket with axial cable outlet
- H4 Biegeradien Kabel ϕ 4.5 mm:
Einmalbiegung: $R > 10$ mm
Dauerbiegung: $R > 50$ mm

Bend radius cable ϕ 4.5 mm:
Rigid configuration: $R > 10$ mm
Frequent flexing: $R > 50$ mm
- H5 Montagesockel mit radialem Kabelausgang
Mounting socket with radial cable outlet
- H6 Anzugsmoment 10 Nm
Torque 10 Nm
- H7 Anzugsmoment 2 Nm, Gewinde reinigen
Torque 2 Nm, clean thread
- H8 Auswechselbarer Späneschutz und Dichtmembrane
Exchangeable protection cover against contamination and sealing diaphragm
- H9 Anzugsmoment 15 Nm, Sicherungsmittel S8 Loctite 222
Torque 15 Nm, locking compound S8 Loctite 222
- H10 4x90° M3 Klemmschrauben, Anzugsmoment 1.3 ± 0.1 Nm
4x90° M3 clamping screw, torque 1.3 ± 0.1 Nm

			ID number: 1110574
			Change No. C000362-11
			Phase: Serie
	Original drawing		TS 150 TS 150 Anschlussmaße / Mating Dimensions
	Scale	Format	
Dimensions in mm	1:1	A3	Allgemeintol. ISO 2768-mH ≤ 6 mm: $\pm 0,2$ General tol. ISO 2768-mH ≤ 6 mm: $\pm 0,2$
The reproduction, distribution and utilization of this document as well as the communication of its contents to others without express authorization is prohibited. Offenders will be held liable for the payment of damages. All rights reserved in the event of the grant of a patent, utility model or design. (ISO 16016)			
HEIDENHAIN DR. JOHANNES HEIDENHAIN GmbH 83301 Traunreut, Germany			Version Revision Sheet Page
			D1198413-00-A-01 Document number