


886 200 A4



Biegeradius min. einmalig 10mm
 Min. bend radius for rigid configuration

max. Kabellänge (L): siehe Techn. Daten des Gerätetyps
 For max. cable length (L): See Specifications of the encoder model

| | | | |
|---|---------------------------|------------|--|
| | | | IDnumber: |
| | | | Change No. C125296-71 Phase: Serie |
|  | Original drawing Scale | Format | Tolerances as per ISO 8015 |
| Dimensions in mm | 1:1 | A4 | General Tolerances ISO 2768:1989-mH $\leq 6\text{mm}$: $\pm 0,2$ |
| AGK 3VB015 --> 3VB15 Anschlussmaße | | | |
| The reproduction, distribution and utilization of this document as well as the communication of its contents to others without express authorization is prohibited. Offenders will be held liable for the payment of damages. All rights reserved in the event of the grant of a patent, utility model or design. (ISO 16016) | | | |
| HEIDENHAIN DR. JOHANNES HEIDENHAIN GmbH 83301 Traunreut, Germany | | Released | Version Revision Sheet |
| | | 21.06.2023 | D 1231810 - 00 - A - 06 Document number |
| | | | 1 of 1 |