



1413962 A3

- (H1) =Klemmbereich / clamping area
- (R) =Referenzmarken-Lage / referencemark position
- (S) =Beginn der Messlänge ML / beginning of measuring length ML

M2,5 für Messeinsatz/
for measuring contacts

Original drawing		ST/MT 12X8 R		Change No.	C126075-11
Scale		MI1218 radial		Phase:	Nicht-Serie
Format		Anschlussmaße / Mating Dimensions		Tolerances as per ISO 8015	
Dimensions in mm	1:1	A3	General Tolerances ISO 2768:1989-mK ≤ 6mm:±0,2		
The reproduction, distribution and utilization of this document as well as the communication of its contents to others without express authorization is prohibited. Offenders will be held liable for the payment of damages. All rights reserved in the event of the grant of a patent, utility model or design. (ISO 16016)					
NUMERIK JENA GmbH Im Semmicht 4 07751 Jena			Released	Version	Revision
			25.08.2023	1336995-00-A-01	
			Document number		1 of 1