





Stecker	Typ	ID-Nr.
Sub-D (Z13)	Specto 12X8R	1336995
Sub-D (Z13)	Specto 12X8R	1371009
Sub-D (Z13)	Metro 12X8R	1371608
Sub-D (Z13)	Metro 12X8R	1371609
Rundstecker M23 (Z14)	Specto 12X8R	1453702
Rundstecker M23 (Z14)	Metro 12X8R	1453717



- (H1) =Klemmbereich / clamping area
- (R) =Referenzmarken-Lage / referencemark position
- (S) =Beginn der Messlänge ML / beginning of measuring length ML

			Change No.	C179777-05
			Phase:	Serie
			Tolerances as per ISO 8015	
			General Tolerances ISO 2768:1989-mK ≤ 6mm:±0,2	
			The reproduction, distribution and utilization of this document as well as the communication of its contents to others without express authorization is prohibited. Offenders will be held liable for the payment of damages. All rights reserved in the event of the grant of a patent, utility model or design. (ISO 16016)	
	Original drawing		ST/MT 12X8 R MI1218 radial Anschlussmaße / Mating Dimensions	
	Scale	Format		
Dimensions in mm	1:1	A3		
NUMERIK JENA GmbH Im Semmicht 4 07751 Jena			Released	Version Revision Sheet Page
			28.05.2025	1336995-01 - A-01 Document number
			1 of 1	