



- Ⓡ = Referenzmarken-Lage Reference mark position
- Ⓜ1 = Klemmbereich Tightening zone
- Ⓜ2 = M2,5/6 tief für Messeinsatz M2,5/6 deep for measuring contact
- Ⓜ3 = Kappe mit Gummiummantelung Cap with rubber coating
- Ⓜ4 = Luftanschluß
(für 2mm-Schlauch) Compressed air input
(for .08" tubing)

MT 12P	11 µAss mit Sub-D-Stecker / 11 µAss with Sub-D male connector	232714-03
MT 12P	11 µAss mit Rundstecker / 11 µAss with round male connector	232714-02

Original drawing		MT 12P		IDnumber:
Scale	Format			Release number: N1046
Dimensions in mm	1:1	A3	Anschlussmaße	Tolerierung nach DIN ISO 8015 Tolerances as per DIN ISO 8015
				Allgemeintoleranzen ISO 2768-mH ±0,2mm; +0,2 General tolerances ISO 2768-mH ±0,2mm; +0,2
The reproduction, distribution and utilization of this document as well as the communication of its contents to others without express authorization is prohibited. Offenders will be held liable for the payment of damages. All rights reserved in the event of the grant of a patent, utility model or design. (ISO 16016)				Version Revision Sheet
HEIDENHAIN DR. JOHANNES HEIDENHAIN GmbH 83301 Traunreut, Germany				D 232716 - 03 - A - 01 Document number
				1 of 1