



bei Dauerbiegebeanspruchung  $R \geq 100$   
 bei einmaliger Biegung  $R \geq 40$   
 For frequent flexing  $R \geq 3.94$ "  
 For rigid configuration  $R \geq 1.57$ "

2 Befestigungsschrauben  
 M4x20 DIN 912  
 2 Flexing screws  
 M4x.79" DIN 912

Original drawing			IDnumber:	
Scale	Format	EXE 6xx /IBV 6xx	Change No.	C116736-10
Dimensions in mm	1:1	A2	Phase:	Serie
Anschlussmaße			Tolerierung nach DIN ISO 8015	
			Tolerances as per DIN ISO 8015	
			Allgemeintoleranzen ISO 2768-mH ±0.2	
			General tolerances ISO 2768-mH ±0.2	
The reproduction, distribution and utilization of this document as well as the communication of its contents to others without express authorization is prohibited. Offenders will be held liable for the payment of damages. All rights reserved in the event of the grant of a patent, utility model or design. ( ISO 16016 )				
<b>HEIDENHAIN</b> DR. JOHANNES HEIDENHAIN GmbH 83301 Traunreut, Germany			Version	Revision
			Sheet	
			1 of 1	
			D 246531 - 02 - A - 01	
			Document number	