



- (R)** = Referenzmarkenlage Reference mark position
- (H1)** = Klemmbereich Tightening zone
- (H2)** = M2,5/6 tief für Messeinsatz M2,5/6 tief für Messeinsatz
- (H3)** = $\varnothing 1.5 +0,005/+0,025$ für auswechselbaren Messstift $\varnothing 1.5 +0.005/+0.025$ for removable measuring tip

| | | |
|-----------------|---------|--------|
| SUB-D | MT 1287 | 376990 |
| SUB-D | MT 1281 | 529502 |
| SUB-D | MT 1271 | 331666 |
| SUB-D | MT 1281 | 359355 |
| SUB-D | MT 1281 | 367137 |
| Interconnectron | MT 1281 | 367137 |
| Interconnectron | MT 1281 | 331314 |
| Interconnectron | MT 1201 | 329350 |

| | | | |
|---|--|--|------------|
| Stecker / Connector | | Typ | ID number: |
| Change No. | | C044210-5 | |
| Phase: | | Serie | |
| Tolerierung nach DIN ISO 8015 | | Tolerances as per DIN ISO 8015 | |
| Allgemeintol. ISO 2768-mH $\leq 6\text{mm}:\pm 0,2$ | | General tol. ISO 2768-mH $\leq 6\text{mm}:\pm 0,2$ | |
| The reproduction, distribution and utilization of this document as well as the communication of its contents to others without express authorization is prohibited. Offenders will be held liable for the payment of damages. All rights reserved in the event of the grant of a patent, utility model or design. (ISO 16016) | | | |
| HEIDENHAIN DR. JOHANNES HEIDENHAIN GmbH 83301 Traunreut, Germany | | Version | Revision |
| D 329365-09-B-01 | | Sheet | Page |
| Document number | | 1 | 1 |