



MT 2501
MT 2581

MT 2571
MT 2581

- (R) = Referenzmarken-Lage Reference mark position
- (H1) = Klemmbereich Tightening zone
- (H2) = M2,5/6 tief für Messeinsatz M2,5/6 deep for measuring contact

Sub-D	MT 2571	F00BD	331667
Sub-D	MT 2581	F00BD	363409
Interconnectron	MT 2581 (Mahr P1526)	F00BD	367138
Interconnectron	MT 2581	F00BD	332104
Interconnectron	MT 2501	F00BD	329351
Stecker / Connector	Typ		IDnumber:

Original drawing			MT 25xx	Tolerierung nach DIN ISO 8015 Tolerances as per DIN ISO 8015
Scale	1:1	Format		
Dimensions in mm			Anschlussmaße	Allgemeintoleranzen ISO 2768-mH ±0,2mm: + 0,2 General tolerances ISO 2768-mH ±0,2mm: + 0,2

The reproduction, distribution and utilization of this document as well as the communication of its contents to others without express authorization is prohibited. Offenders will be held liable for the payment of damages. All rights reserved in the event of the grant of a patent, utility model or design. (ISO 16016)