



bei Dauerbiegebeanspruchung $R \geq 100$
 bei einmaliger Biegung $R \geq 40$
 For frequent flexing $R \geq 3.94$ "
 For rigid configuration $R \geq 1.57$ "

2 Befestigungsschrauben
 M4x20 DIN 912

2 Flexing screws
 M4x.79" DIN 912

HEIDENHAIN

		IDnumber:	
		Change No. C116736-05	
		Phase: Serie	
		Tolerierung nach DIN ISO 8015	
		Tolerances as per DIN ISO 8015	
		Allgemeintoleranzen ISO 2768-mH ± 0.2	
		General tolerances ISO 2768-mH ± 0.2	
The reproduction, distribution and utilization of this document as well as the communication of its contents to others without express authorization is prohibited. Offenders will be held liable for the payment of damages. All rights reserved in the event of the grant of a patent, utility model or design. (ISO 16016)			
		Original drawing	EXE 606 /IBV 606
Dimensions in mm		Scale	Format
		1:1	A2
		Anschlussmaße	
		Version	Revision
		Sheet	
		1 of 1	
		D 337485 -01-A-01	
		Document number	

HEIDENHAIN
 DR. JOHANNES HEIDENHAIN GmbH
 83301 Traunreut, Germany