



HEIDENHAIN

Montageanleitung
Mounting Instructions
Instructions de montage
Istruzioni di montaggio
Instrucciones de montaje

RON 706
RON 706 C




8/2001

— |

| —

— |


| —













Stirnseitige Wellenankopplung
Shaft coupling on end face
accouplement sur l'arbre par la face frontale
accoppiamento albero frontale
acoplamiento frontal del eje




Ⓚ = Kundenseitige Anschlussmaße
Required mating dimensions
conditions requises pour le montage
quote per il montaggio
cotas de montaje requeridas


ⓐ = Lagerdrehachse der Kundenwelle (Rotor)
Bearing axis of customer's shaft
axe de rotation du montage de l'arbre moteur (rotor)
asse cuscinetto dell'albero cliente (Rotore)
eje de rodamiento del eje del cliente (rótor)








		 $T \geq -10\text{ °C}$ (14 °F)		<p>IP 40 EN 60529</p> <p>IP 64 EN 60529</p>
<p>Ø 6 mm</p>	<p>$R_1 \geq 20\text{ mm}$</p>	<p>$R_2 \geq 75\text{ mm}$</p>		<p>$M_d \leq 0.06\text{ Nm}$ (20 °C; IP 40)</p> <p>$M_d \leq 0.5\text{ Nm}$ (20 °C; IP 64)</p> <p>$I = 1.2 \cdot 10^{-3}\text{ kgm}^2$</p>
<p>Ø 8 mm</p> 	<p>$R_1 \geq 40\text{ mm}$</p>	<p>$R_2 \geq 100\text{ mm}$</p>		
 <p>°C (°F)</p>	 <p>0 ... 50 °C (32 ... 122 °F)</p>		 <p>-30 ... 80 °C (-22 ... 176 °F)</p>	







Id.-Nr. 291 697-03




1) Außenschirm auf Gehäuse
External shield on housing
 blindage externe sur boîtier
 schermo esterno sulla carcassa
 blindaje externo a carcasa

2) Innenschirm
Internal shield
 blindage interne
 schermo interno
 blindaje interno

1	2	5	6	7	8	3	4	1)	9
I ₁		I ₂		I ₀		5V U _P	0V U _N		2)
+	-	+	-	+	-				
grün green vert verde verde	gelb yellow jaune giallo amarillo	blau blue bleu azzurro azul	rot red rouge rosso rojo	grau gray gris grigio gris	rosa pink rose rosa rosa	braun brown brun marrone marrón	weiß white blanc bianco blanco		weiß/braun white/brown blanc/brun bianco/marrone blanco/marrón

EN 50 178





HEIDENHAIN

DR. JOHANNES HEIDENHAIN GmbH


Dr.-Johannes-Heidenhain-Straße 5


83301 Traunreut, Germany


 +49/86 69/31-0

 +49/86 69/50 61

e-mail: info@heidenhain.de

 **Service** +49/86 69/31-12 72

 TNC-Service +49/86 69/31-14 46

 +49/86 69/98 99

e-mail: service@heidenhain.de

www.heidenhain.de

Ve 00

363 475-91 · 5 · 2/2002 · F&W · Printed in Germany

Änderungen vorbehalten · *Subject to change without notice* · Sous réserve de modifications · *Con riserva di modifiche* · Sujeto a modificaciones

