



ST 3088/3089
ST 3008/3009

UNC 4/40

ST 3078/3079

ST 3009	510571-
ST 3088 (Sub-D)	384007-
ST 3088	375131-
ST 3078	375133-
ST 3008	375129-

ID number: 375129-03	
Change No. Serie	
Phase: Serie	
Tolerierung nach DIN ISO 8015 Tolerances as per DIN ISO 8015	
Allgemeintol. ISO 2768-mH ≤6mm:±0,2 General tol. ISO 2768-mH ≤6mm:±0,2	

The reproduction, distribution and utilization of this document as well as the communication of its contents to others without express authorization is prohibited. Offenders will be held liable for the payment of damages. All rights reserved in the event of the grant of a patent, utility model or design. (ISO 16016)

HEIDENHAIN DR. JOHANNES HEIDENHAIN GmbH 83301 Traunreut, Germany	Version	Revision	Sheet	Page
	D 365665-01 - C - 1 Document number			

Modellname: 375129-03-B04 Version: ***
 886.200 A3
 886.200 A3

- H1** = Klemmbereich tightening zone
- R** = Referenzmarken-Lage Reference mark position
- S** = Beginn der Messlänge ML Beginning of measuring length ML