



ST 3088/3089
ST 3008/3009

UNC 4/40

ST 3078/3079

M2,5 für Messeinsatz
for measuring contacts

- (H1)** = Klemmbereich tightening zone
- (R)** = Referenzmarken-Lage Reference mark position
- (S)** = Beginn der Messlänge ML Beginning of measuring length ML

ST 3088 (Sub-D)		384008-
ST 3088		375132-
ST 3078		375134-
ST 3008		375130-
ID number:		375130-03
Change No.		Serie
Phase:		Serie
Tolerierung nach DIN ISO 8015 Tolerances as per DIN ISO 8015		
Allgemeintol. ISO 2768-mH ≤6mm:±0,2 General tol. ISO 2768-mH ≤6mm:±0,2		
The reproduction, distribution and utilization of this document as well as the communication of its contents to others without express authorization is prohibited. Offenders will be held liable for the payment of damages. All rights reserved in the event of the grant of a patent, utility model or design. (ISO 16016)		
 DR. JOHANNES HEIDENHAIN GmbH 83301 Traunreut, Germany		Version Revision Sheet Page D 366130-01 - B - 1 1 of 1