



ST 3083/3087  
ST 3003/3007

UNC 4/40

ST 3073/3077

ST 3087 (Sub-D)		384006-
ST 3087		375136-
ST 3077		375137-
ST 3007		375135-
ID number:		375135-03
Change No.		
Phase:		Serie
Original drawing		ST 30x3/7 axial Redesign ST 30x7 Anschlussmaße / Mating Dimensions
Scale   Format		
Dimensions in mm	4:5   A3	Tolerances as per ISO 8015
		General Tolerances ISO 2768:1989-mH $\leq 6\text{mm}:\pm 0,2$

- H1** = Klemmbereich                      tightening zone
- H2** = Luftanschluss für 2 mm Schlauch      air supply for 2 mm tube
- R** = Referenzmarken-Lage                      Reference mark position
- S** = Beginn der Messlänge ML                      Beginning of measuring length ML

Modellname: 375135-03-B04    Version: \*\*\*

886 200 A3