



C4	Anschluss-Belegung	
	Elektrischer Anschluss	
	Geometrie Polbild (Steckseite)	
AMO	Firmenname	
..	Ausgangssignal	..
..	Eingangssignal	..
EnDat22	Datenschnittstelle	EnDat22
..	Teilkreiszusatzspur	..
8 polig	Kundenseitige Steckerausführung	Ader
5	Versorgung 0V (Un)	weißgrün
1	Versorgung 0V (Sensorleitung)	weiß
8	Versorgung +V (Up)	braungrün
2	Versorgung +V (Sensorleitung)	blau
Im Messgerät	Versorgung verbunden mit Sensorleitung	Im Messgerät
Gehäuse	Außenschirm	Schirm
3	Serielle Schnittstelle Daten	grau
4	Serielle Schnittstelle Daten invers	rosa
7	Serielle Schnittstelle Takt	violett
6	Serielle Schnittstelle Takt invers	gelb

C4	Pin configuration	
	Electrical connection	
	Geometry of pole pattern (plug side)	
AMO	company name	
..	Output signal	..
..	Input signal	..
EnDat22	Data interface	EnDat22
..	Additional circular scale track	..
8-pin	Customer's connection version	Wire
5	Supply 0V (Un)	white and green
1	Supply 0V (sensor line)	white
8	Supply +V (Up)	brown and green
2	Supply +V (sensor line)	blue
In the encoder	Supply connected with sensor line	In the encoder
Housing	External shield	Shield
3	Serial interface for data	grey
4	Serial interface for data, inverse	pink
7	Serial interface for clock	violet
6	Serial interface for clock, inv.	yellow