



R8	Anschluss-Belegung
	Elektr. Anschluss
	Geometrie Polbild (Steckseite)
..	Ausgangssignal
..	Eingangssignal
EnDat22	Datenschnittstelle
..	Teilkreiszusatzspur
15 polig	Kundenseitige Steckerausführung
14	Versorgung 0V (Un)
13	Versorgung +V (Up)
Im Messgerät	Versorgung verbunden mit Fühlleitung
7	Serielle Schnittstelle Daten
8	Serielle Schnittstelle Daten invers
9	Serielle Schnittstelle Takt
10	Serielle Schnittstelle Takt invers
1	Freie Litzen und Pins
2	Freie Litzen und Pins
3	Freie Litzen und Pins
4	Freie Litzen und Pins
5	Freie Litzen und Pins
6	Freie Litzen und Pins
15	Freie Litzen und Pins
11	Freie Litzen und Pins
12	Freie Litzen und Pins

R8	Pin configuration
	Electrical connection
	Geometry of pole pattern (plug side)
..	Output signal
..	Input signal
EnDat22	Data interface
..	Additional circular-scale track
15 polig	Customer's connection version
14	Supply 0 V (Un)
13	Supply +V (Up)
in encoder	Supply connected with sensor line
7	Serial interface for data
8	Serial interface for data, inverse
9	Serial interface for clock
10	Serial interface for clock, inverse
1	Free wires and pins
2	Free wires and pins
3	Free wires and pins
4	Free wires and pins
5	Free wires and pins
6	Free wires and pins
15	Free wires and pins
11	Free wires and pins
12	Free wires and pins