



| | | |
|---|--|--------------|
| JB | Anschluss-Belegung | |
|  | Elektrischer Anschluss | |
|  | Geometrie Polbild (Steckseite) | |
| JH | Firmenname | JH |
| .. | Ausgangssignal | .. |
| .. | Eingangssignal | .. |
| Mitsu | Datenschnittstelle | Mitsu |
| .. | Teilkreiszusatzspur | .. |
| 10 polig | Kundenseitige Steckerausführung | Ader |
| 2 | Versorgung 0V (Un) | weißgrün |
| 1 | Versorgung +V (Up) | braungrün |
| Gehäuse | Außenschirm | Schirm |
| 7 | Serielle Schnittstelle Daten | grau |
| 8 | Serielle Schnittstelle Daten invers | rosa |
| 3 | Serielle Schnittstelle Request Frame | violett |
| 4 | Serielle Schnittstelle Request Frame inv | gelb |
| 5;6;9;10 | Freie Adern und Pins | |
| | Freie Adern und Pins | blau |
| | Freie Adern und Pins | weiß |

| | | |
|---|---|-----------------|
| JB | Pin configuration | |
|  | Electrical connection | |
|  | Geometry of pole pattern (plug side) | |
| JH | company name | JH |
| .. | Output signal | .. |
| .. | Input signal | .. |
| Mitsu | Data interface | Mitsu |
| .. | Additional circular scale track | .. |
| 10-pin | Customer's connection version | Wire |
| 2 | Supply 0V (Un) | white and green |
| 1 | Supply +V (Up) | brown and green |
| Housing | External shield | Shield |
| 7 | Serial interface for data | grey |
| 8 | Serial interface for data, inverse | pink |
| 3 | Serial interface Request Frame | violet |
| 4 | Serial interface Request Frame, inv. | yellow |
| 5;6;9;10 | Free wires and pins | |
| | Free wires and pins | blue |
| | Free wires and pins | white |

| | | | |
|--|------------|----------------|------------|
| Connection layout JB 0BB10 .. Mitsu JH | Pin Layout | Change No: C04 | C043455-05 |
|--|------------|----------------|------------|

The reproduction, distribution and utilization of this document as well as the communication of its contents to others without express authorization is prohibited.