





Ansicht von unten  
Bottom view



Ansicht von hinten  
Back view



		ID number: 1037960-01	
		Release number: N2439	
		Tolerierung nach DIN ISO 8015 Tolerances as per DIN ISO 8015	
		Allgemeintol. ISO 2768-mH $\pm 0.2$ General tol. ISO 2768-mH $\pm 0.2$	
The reproduction, distribution and utilization of this document as well as the communication of its contents to others without express authorization is prohibited. Offenders will be held liable for the payment of damages. All rights reserved in the event of the grant of a patent, utility model or design. (ISO 16016)			
Original drawing Scale: 7:10 Format: A2		<b>EIB 742</b> Anschlussmaße	
Dimensions in mm		Version   Revision   Sheet   Page <b>D 631432-00-A-03</b> Document number	
<b>HEIDENHAIN</b> DR. JOHANNES HEIDENHAIN GmbH 83301 Traunreut, Germany		1 of 1	