



866 200 A3

|   |                           |                        |  |
|---|---------------------------|------------------------|--|
|   |                           |                        | IDnumber:  |
|   |                           |                        | Change No. C063396-5<br>Phase: Serie   |
|   | Original drawing<br>Scale | Format                 | APK SpeedTEC-Stecker Bu / Sub-D 26pol. S<br>Anschlussmaße                    |
| Dimensions<br>in mm   | 1:1                       | A3                     | Tolerances as per<br>ISO 8015<br>General Tolerances<br>ISO 2768:1989-mH ±0.2 |
| The reproduction, distribution and utilization of this document as well as the communication of its contents to others without express authorization is prohibited. Offenders will be held liable for the payment of damages. All rights reserved in the event of the grant of a patent, utility model or design. ( ISO 16016 ) |                           |                        |  |
| <b>HEIDENHAIN</b><br>DR. JOHANNES HEIDENHAIN GmbH<br>83301 Traunreut, Germany   |                           | Released<br>13.12.2017 | Version   Revision   Sheet<br>D 645858 - 00 - B - 21<br>Document number      |
|   |                           |                        | 1<br>of<br>1   |