


L +1% bzw. 30mm



- Biegeradius min. dauernd 100mm
- Biegeradius min. einmalig 40mm
- Schleppkettenradius min. 100mm

max. Kabellänge (L): siehe Techn. Daten des Gerätetyps

		IDnumber:	
		Change No. C128655-35	
		Phase: Serie	
	Original drawing	VBK M23-SpeedTEC Bu / M23-SpeedTEC Sti 8	
	Scale	Anschlussmaße	
	Format		
Dimensions in mm	1:1	A3	Tolerances as per ISO 8015
			General Tolerances ISO 2768:1989-mH ±0.2
The reproduction, distribution and utilization of this document as well as the communication of its contents to others without express authorization is prohibited. Offenders will be held liable for the payment of damages. All rights reserved in the event of the grant of a patent, utility model or design. (ISO 16016)			
HEIDENHAIN		Released	Version Revision Sheet
DR. JOHANNES HEIDENHAIN GmbH		01.12.2022	D 645858 - 00 - B - 25
83301 Traunreut, Germany		Document number	
		1 of 1	