



Biegeradius min. dauernd 100mm
 Biegeradius min. einmalig 40mm
 Schleppkettenradius min. 100mm

max. Kabellänge (L): siehe Techn. Daten des Gerätetyps

			IDnumber:
			Change No. C128655-35 Phase: Serie
	Original drawing Scale	Format	APK M23-SpeedTEC Bu / Sub-D 25pol. Bu 8m Anschlussmaße
Dimensions in mm	1:1	A3	
			Tolerances as per ISO 8015
			General Tolerances ISO 2768:1989-mH ±0.2
The reproduction, distribution and utilization of this document as well as the communication of its contents to others without express authorization is prohibited. Offenders will be held liable for the payment of damages. All rights reserved in the event of the grant of a patent, utility model or design. (ISO 16016)			
HEIDENHAIN DR. JOHANNES HEIDENHAIN GmbH 83301 Traunreut, Germany		Released 01.12.2022	Version Revision Sheet D 645858 - 00 - B - 26 Document number
			1 of 1