



Biegeradius min. dauernd
Min. bend radius for flexing 50mm

Biegeradius min. einmalig
Min. bend radius for rigid configuration 18mm



Schleppkettenradius min.
Min. drag chain radius 50mm

max. Kabellänge (L): siehe Techn. Daten des Gerätetyps
For max. cable length (L): See Specifications of the encoder model



			IDnumber:
			Change No. C014973-10 Phase: Serie
	Original drawing Scale	Format	Tolerierung nach DIN ISO 8015 Tolerances as per DIN ISO 8015
Dimensions in mm	1:1	A4	Allgemeintoleranzen ISO 2768-mH ±0,2mm: +- 0,2 General tolerances ISO 2768-mH ±0,2mm: +- 0,2
		AGK FCI --> Sub-D (16S15)	
		Anschlussmaße	

The reproduction, distribution and utilization of this document as well as the communication of its contents to others without express authorization is prohibited. Offenders will be held liable for the payment of damages. All rights reserved in the event of the grant of a patent, utility model or design. (ISO 16016)

HEIDENHAIN
DR. JOHANNES HEIDENHAIN GmbH
83301 Traunreut, Germany

Document number		
D 652661 - 00 - A - 54		
Version	Revision	Sheet
		1 of 1