



Biegeradius min. dauernd Min. bend radius for flexing	--
Biegeradius min. einmalig Min. bend radius for rigid configuration	10mm
Schleppkettenradius min. Min. drag chain radius	--
max. Kabellänge (L): siehe Techn. Daten des Gerätetyps For max. cable length (L): See Specifications of the encoder model	

auf Flachdichtung achten
 pay attention to flat gasket

Codiernase

4x Ø 2,7

Lochkreis-Durchmesser 28mm
 bolt-hole circle diameter 28mm

kundenseitige Anschlussmaße siehe D1140890 Bl.01
 required mating dimensions see D1140890 Bl.01

		IDnumber:	
		Change No. C114376-63 Phase: Serie	
	Original drawing Scale	Format	AGK JAE --> Flanschdose M12 (AFS08)
Dimensions in mm	1:1	A3	Anschlussmaße
Tolerances as per ISO 8015 General Tolerances ISO 2768:1989-mH ±0.2			
The reproduction, distribution and utilization of this document as well as the communication of its contents to others without express authorization is prohibited. Offenders will be held liable for the payment of damages. All rights reserved in the event of the grant of a patent, utility model or design. (ISO 16016)			
HEIDENHAIN DR. JOHANNES HEIDENHAIN GmbH 83301 Traunreut, Germany		Released 17.01.2023	Version Revision Sheet D 652661 - 00 - A - 69 1 of 1
		Document number	