



Biegeradius min. dauernd  
Min. bend radius for flexing 55mm

Biegeradius min. einmalig  
Min. bend radius for rigid configuration 18mm

Schleppkettenradius min.  
Min. drag chain radius --

max. Kabellänge (L): siehe Techn. Daten des Gerätetyps  
For max. cable length (L): See Specifications of the encoder model

			IDnumber:
			Change No. C125296-72 Phase: Serie
			Tolerances as per ISO 8015
			General Tolerances ISO 2768:1989-mH ±0.2
	Original drawing Scale	Format	AGK FCI 90B12 --> Sub-D (16S15)
Dimensions in mm	1:1	A3	Anschlussmaße
The reproduction, distribution and utilization of this document as well as the communication of its contents to others without express authorization is prohibited. Offenders will be held liable for the payment of damages. All rights reserved in the event of the grant of a patent, utility model or design. ( ISO 16016 )			
<b>HEIDENHAIN</b> DR. JOHANNES HEIDENHAIN GmbH 83301 Traunreut, Germany		Released 21.06.2023	Version   Revision   Sheet D 652661 - 00 - A - 73 1 of 1
		Document number	