



Biegeradius min. dauernd
Min. bend radius for flexing 50mm

Biegeradius min. einmalig
Min. bend radius for rigid configuration 10mm

Schleppkettenradius min.
Min. drag chain radius 50mm

max. Kabellänge (L): siehe Techn. Daten des Gerätetyps
For max. cable length (L): See Specifications of the encoder model

| | | | |
|--|---------------------------|------------------------|--|
| | | | IDnumber: |
| | | | Change No. C125296-72 Phase: Serie |
| | Original drawing Scale | Format | Tolerances as per ISO 8015 |
| Dimensions in mm | 1:1 | A3 | General Tolerances ISO 2768:1989-mH $\pm 0,2$ |
| AGK FCI 90B14 --> Sub-D (16S15) Anschlussmaße | | | |
| The reproduction, distribution and utilization of this document as well as the communication of its contents to others without express authorization is prohibited. Offenders will be held liable for the payment of damages. All rights reserved in the event of the grant of a patent, utility model or design. (ISO 16016) | | | |
| HEIDENHAIN DR. JOHANNES HEIDENHAIN GmbH 83301 Traunreut, Germany | | Released 21.06.2023 | Version Revision Sheet D 652661 - 00 - A - 74 1 of 1 |
| | | Document number | |