



Biegeradius min. dauernd
Min. bend radius for flexing --

Biegeradius min. einmalig
Min. bend radius for rigid configuration 24mm

Schleppkettenradius min.
Min. drag chain radius --



max. Kabellänge (L): siehe Techn. Daten des Gerätetyps
For max. cable length (L): See Specifications of the encoder model

886 200 A4

			IDnumber:
			Change No. C122566-05 Phase: Serie
	Original drawing Scale	Format	Tolerances as per ISO 8015
Dimensions in mm	1:1	A4	General Tolerances ISO 2768:1989-mH ≅ 6mm: +- 0,2

The reproduction, distribution and utilization of this document as well as the communication of its contents to others without express authorization is prohibited. Offenders will be held liable for the payment of damages. All rights reserved in the event of the grant of a patent, utility model or design. (ISO 16016)

HEIDENHAIN DR. JOHANNES HEIDENHAIN GmbH 83301 Traunreut, Germany	Released	Version	Revision	Sheet
	28.11.2022	D 652661 - 01 - A - 62		1 of 1
Document number				1