



- (H1) = Taststiftaufnahme M3  
Stylus holder M3
- (H2) = Auswechselbare Taststifte nach Typenübersicht D295695  
Exchangeable styli as per table of types D295695
- (H3) = Verschraubungs-Kit Id.Nr. 643089-01
- (H4) = Anzugsmoment 10Nm, Sicherungsmittel S8 Loctite 222  
torque 10Nm, Locking compound S8 Loctite 222
- (H5) = Anzugsmoment 10Nm± 1Nm  
torque 10Nm± 1Nm
- (H6) = Anzugsmoment 2Nm, Gewinde reinigen  
torque 2Nm, clean thread
- (H7) = Bezugsebene Kabelausgang  
reference plane cable outlet

TS 261, axialer Kabelausgang, M12, EnDat	1146747--
TS 248, axialer Kabelausgang, M12	683110--
TS 260, axialer Kabelausgang, M12	738082--

Original drawing		TS 26x, axialer Kabelausgang		ID number:	
Scale		TS 26x, axial cable outlet		Change No. C121536-32	
Format		Anschlussmaße / Mating Dimensions		Serie	
Dimensions in mm	1:1	A2	Tolerierung nach DIN ISO 8015 Tolerances as per DIN ISO 8015		
			Allgemeintol. ISO 2768-mH ±6mm± 0,2 General tol. ISO 2768-mH ±6mm± 0,2		
The reproduction, distribution and utilization of this document as well as the communication of its contents to others without express authorization is prohibited. Offenders will be held liable for the payment of damages. All rights reserved in the event of the grant of a patent, utility model or design. (ISO 16016)					
<b>HEIDENHAIN</b> DR. JOHANNES HEIDENHAIN GmbH 83301 Traunreut, Germany			Version		Page
			D 738098-03 - A-01		1 of 1
			Document number		