



866 200 A3

|  |                           |                        |  |
|--|---------------------------|------------------------|--|
|  |                           |                        | IDnumber:  |
|  |                           |                        | Change No. C142942-15<br>Phase: Serie                          |
|  | Original drawing<br>Scale | Format                 | APK M12-Stecker/Buchsengehäuse 91<br>Anschlussmaße             |
| Dimensions<br>in mm  | 1:1                       | A3                     |  |
|  |                           |                        | Tolerances as per<br>ISO 8015                                  |
|  |                           |                        | General Tolerances<br>ISO 2768:1989-mH $\pm 0,2$               |
| The reproduction, distribution and utilization of this document as well as the communication of its contents to others without express authorization is prohibited.<br>Offenders will be held liable for the payment of damages. All rights reserved in the event of the grant of a patent, utility model or design. ( ISO 16016 ) |                           |                        |  |
| <b>HEIDENHAIN</b><br>DR. JOHANNES HEIDENHAIN GmbH<br>83301 Traunreut, Germany  |                           | Released<br>04.10.2022 | Version   Revision   Sheet<br>D 896711 - 00 - A - 44<br>1 of 1 |
|  |                           | Document number        |  |