





Maße in mm  
Dimensions in mm  
cotes en mm  
dimensioni in mm  
dimensiones en mm



**K 17**  
Id.-Nr. 296 746-xx




# HEIDENHAIN

Montageanleitung  
Mounting Instructions  
Instructions de montage  
Istruzioni di montaggio  
Instrucciones de montaje

## ROQ 425 ROC 413 PROFIBUS-DP

1/2002



**DR. JOHANNES HEIDENHAIN GmbH**

Dr.-Johannes-Heidenhain-Straße 5

83301 Traunreut, Germany

☎ +49 (8669) 31-0

FAX +49 (8669) 5061

E-Mail: info@heidenhain.de

**Technical support** ☎ +49 (8669) 31-1000

**Measuring systems** ☎ +49 (8669) 31-31 04

E-Mail: service.ms-support@heidenhain.de

**TNC support** ☎ +49 (8669) 31-31 01

E-Mail: service.nc-support@heidenhain.de

**NC programming** ☎ +49 (8669) 31-31 03

E-Mail: service.nc-pgm@heidenhain.de

**PLC programming** ☎ +49 (8669) 31-31 02

E-Mail: service.plc@heidenhain.de

**Lathe controls** ☎ +49 (7 11) 95 28 03-0

E-Mail: service.hsf@heidenhain.de

[www.heidenhain.de](http://www.heidenhain.de)







Ve 00


345 743-92 · 6 · 7/2006 · E · Printed in Germany · Änderungen vorbehalten

Subject to change without notice · Sous réserve de modifications · Con riserva di modifiche · Sujeto a modificaciones






**Kabelvorbereitung**  
**Preparing the cable**  
**Préparation du câble**  
**Preparazione del cavo**  
**Preparación del cable**



Up = 10 ... 30 V  
(max. 125 mA → 24 V)

EN 50 178/4.98; 5.2.9.5  
IEC 364-4-41: 1992; 411(PELV/SELV)  
(siehe, see, voir, vedi, véase  
HEIDENHAIN D 231 929)




LED-BUS


LED-POWER

grün  
green  
vert  
verde  
verde

OK ✓



max. 40 N (≤ 6 000 min<sup>-1</sup>)  
max. 10 N (≤ 10 000 min<sup>-1</sup>)



max. 60 N (≤ 6 000 min<sup>-1</sup>)  
max. 20 N (≤ 10 000 min<sup>-1</sup>)