



HEIDENHAIN



Montageanleitung
Mounting Instructions
Instructions de montage
Istruzioni di montaggio
Instrucciones de montaje

ROD 700
ROD 700 C


8/2001






1.



2.




DIN EN 100 015 - 1
CECC 00015 - 1




mm




TOLERANCING ISO 8015
ISO 2768 - m H














A = Lagerung
 Bearing
 roulement
 cuscinetto
 rodamiento



	K 01: $\lambda \leq 0.3 \text{ mm}$	K 15: $\lambda \leq 0.3 \text{ mm}$	K 16: $\lambda \leq 0.3 \text{ mm}$
	K 01: $\alpha \leq 0.5^\circ$	K 15: $\alpha \leq 0.2^\circ$	K 16: $\alpha \leq 0.5^\circ$
	K 01: $\delta \leq 0.2 \text{ mm}$	K 15: $\delta \leq 0.1 \text{ mm}$	K 16: $\delta \leq 1 \text{ mm}$




		 $T \geq -10\text{ °C}$ (14 °F)
$\text{Ø } 6\text{ mm}$	$R_1 \geq 20\text{ mm}$	$R_2 \geq 75\text{ mm}$
 $\text{Ø } 8\text{ mm}$	$R_1 \geq 40\text{ mm}$	$R_2 \geq 100\text{ mm}$

	max. 30 N
	max. 30 N

	 0 ... 50 °C (32 ... 122 °F)
	 -30 ... 80 °C (-22 ... 176 °F)


	IP 64 EN 60 529
	$M_d \leq 0.012\text{ Nm (20 °C)}$ $I = 0.36 \cdot 10^{-3}\text{ kgm}^2$




$U_P = 5\text{ V} \pm 5\%$
(max. 90 mA)




EN 50 178



$$n \leq \begin{cases} \frac{90}{18\,000} \cdot 10^3 \cdot 60\text{ min}^{-1} (-3\text{dB}) = 300\text{ min}^{-1} (-3\text{dB}) \\ 1\,000\text{ min}^{-1} \end{cases}$$




I_1, I_2, I_0






ROD 700: 1xI₀
ROD 700C: 36xI₀

I_1, I_2





I_0





RC 4157
 $C = 27 \text{ pF}$
 $R = 100 \text{ k}\Omega$
 $U_1 = 2.5 \text{ V}$

Id.-Nr. 291 697-03




1) Außenschirm auf Gehäuse
External shield on housing
 blindage externe sur boîtier
schermo esterno sulla carcassa
 blindaje externo a carcasa

2) Innenschirm
Internal shield
 blindage interne
schermo interno
 blindaje interno

1	2	5	6	7	8	3	4	1)	9
I ₁		I ₂		I ₀		5V U _P	0V U _N		2)
+	-	+	-	+	-				
grün <i>green</i> vert verde verde	gelb <i>yellow</i> jaune giallo amarillo	blau <i>blue</i> bleu azzurro azul	rot <i>red</i> rouge rosso rojo	grau <i>gray</i> gris grigio gris	rosa <i>pink</i> rose rosa rosa	braun <i>brown</i> brun marrone marrón	weiß <i>white</i> blanc bianco blanco		weiß/braun <i>white/brown</i> blanc/brun bianco/marrone blanco/marrón

EN 50 178




HEIDENHAIN

DR. JOHANNES HEIDENHAIN GmbH


Dr.-Johannes-Heidenhain-Straße 5


83301 Traunreut, Germany


 +49/86 69/31-0

 +49/86 69/50 61

e-mail: info@heidenhain.de

 **Service** +49/86 69/31-12 72

 TNC-Service +49/86 69/31-14 46

 +49/86 69/98 99

e-mail: service@heidenhain.de

<http://www.heidenhain.de>

