



- (R) = Referenzmarken-Lage Reference mark position
- (H1) = Klemmbereich Tightening zone
- (H2) = M2.5/6 tief für Messeinsatz M2.5/6 deep for measuring contact
- (H3) = Druckluftanschluss (für 2mm-Schlauch) Compressed air input (for .08" tubing)

SUB-D	MT 1287	F00BC	376990
Interconnectron	MT 1287	011AD	375162
Stecker / Connector	Typ		ID number: 375162-01

	Original drawing		MT 12x7 Anschlussmaße	Release number: N1046 Tolerierung nach DIN ISO 8015 Tolerances as per DIN ISO 8015 Allgemeintol. ISO 2768-mH ≤6mm:±0,2 General tol. ISO 2768-mH ≤6mm:±0,2
	Scale	Format		
Dimensions in mm	1:1	A3		

The reproduction, distribution and utilization of this document as well as the communication of its contents to others without express authorization is prohibited. Offenders will be held liable for the payment of damages. All rights reserved in the event of the grant of a patent, utility model or design. (ISO 16016)