




<b>TV</b>	<b>Anschluss-Belegung</b>	
	<b>Elektr. Anschluss</b>	
	<b>Geometrie Polbild (Steckseite)</b>	
<b>JH</b>	<b>Firmenname</b>	<b>JH</b>
..	<b>Ausgangssignal</b>	..
..	<b>Eingangssignal</b>	..
<b>DQ01</b>	<b>Datenschnittstelle</b>	<b>DQ01</b>
..	<b>Teilkreiszusatzspur</b>	..
8 polig	Kundenseitige Steckerausführung	Litzen
5	Versorgung 0V (Un)	weißgrün
1	Versorgung +V (Up)	weiß
Gehäuse	Außenschirm	Schirm
3	Serielle Schnittstelle RXP	grau
4	Serielle Schnittstelle RXN	rosa
7	Serielle Schnittstelle TXP	violett
6	Serielle Schnittstelle TXN	gelb
2	Freie Litzen und Pins	blau
8	Freie Litzen und Pins	braungrün
0060	Ergänzungen	

0060 = Freie Litzen und Pins dürfen nicht belegt werden!

<b>TV</b>	<b>Connection layout</b>	
	<b>Electrical connection</b>	
	<b>Geometry of pole pattern (plug side)</b>	
<b>JH</b>	<b>company name</b>	<b>JH</b>
..	<b>Output signal</b>	..
..	<b>Input signal</b>	..
<b>DQ01</b>	<b>Data interface</b>	<b>DQ01</b>
..	<b>Additional circular-scale track</b>	..
8-pin	Customer's connection version	litzes
5	Supply 0 V (Un)	whitegreen
1	Supply +V (Up)	white
housing	External shield	shield
3	Serial interface for RXP	grey
4	Serial interface for RXN	pink
7	Serial interface for TXP	violet
6	Serial interface for TXN	yellow
2	Free wires and pins	blue
8	Free wires and pins	browngreen
0060	Additions	

0060 = Vacant pins or wires must not be used!

Connection layout TV 1SS08 .. DQ01 .. .. JH		Pin Layout		Change No:C019789-26										
The reproduction, distribution and utilization of this document as well as the communication of its contents to others without express authorization is prohibited. Offenders will be held liable for the payment of damages. All rights reserved in the event of the grant of a patent, utility model or design.														
<b>HEIDENHAIN</b> DR. JOHANNES HEIDENHAIN GmbH 83301 Traunreut, Germany		<table border="1"> <tr> <td>Serie</td> <td>Version</td> <td>Revision</td> <td>Sheet</td> <td>Page</td> </tr> <tr> <td><b>D781766</b></td> <td><b>- 00</b></td> <td><b>- A</b></td> <td><b>- 06</b></td> <td>1/1</td> </tr> </table>	Serie	Version	Revision	Sheet	Page	<b>D781766</b>	<b>- 00</b>	<b>- A</b>	<b>- 06</b>	1/1	Document No	
Serie	Version	Revision	Sheet	Page										
<b>D781766</b>	<b>- 00</b>	<b>- A</b>	<b>- 06</b>	1/1										