





<b>NW</b>	<b>Anschluss-Belegung</b>
	<b>Elektrischer Anschluss</b>
	<b>Geometrie Polbild (Steckseite)</b>
<b>JH</b>	<b>Firmenname</b>
<b>LD/PP</b>	<b>Ausgangssignal</b>
..	<b>Eingangssignal</b>
..	<b>Datenschnittstelle</b>
<b>KC0</b>	<b>Teilkreiszusatzspur</b>
15 polig	Kundenseitige Steckerausführung
14	Versorgung 0V (Un)
13	Versorgung +V (Up)
1	Rechteck-Signal Ua1
2	Rechteck-Signal Ua1 invers
3	Rechteck-Signal Ua2
4	Rechteck-Signal Ua2 invers
5	Rechteck-Signal Ua0
6	Rechteck-Signal Ua0 invers
7	Kommutierungssignal U
9	Kommutierungssignal V
11	Kommutierungssignal W
8	Freie Adern und Pins
10	Freie Adern und Pins
12	Freie Adern und Pins
15	Freie Adern und Pins
0078	Ergänzungen

0078= Pin 15 darf nicht belegt werden! Nur für interne Zwecke!

<b>NW</b>	<b>Pin configuration</b>
	<b>Electrical connection</b>
	<b>Geometry of pole pattern (plug side)</b>
<b>JH</b>	<b>company name</b>
<b>LD/PP</b>	<b>Output signal</b>
..	<b>Input signal</b>
..	<b>Data interface</b>
<b>KC0</b>	<b>Additional circular scale track</b>
15-pin	Customer's connection version
14	Supply 0V (Un)
13	Supply +V (Up)
1	Square-wave signal Ua1
2	Square-wave signal Ua1 inverse
3	Square-wave signal Ua2
4	Square-wave signal Ua2 inverse
5	Square-wave signal Ua0
6	Square-wave signal Ua0 inverse
7	Commutation signal U
9	Commutation signal V
11	Commutation signal W
8	Free wires and pins
10	Free wires and pins
12	Free wires and pins
15	Free wires and pins
0078	Additions

0078= Pin 15 must not be used! Only for internal purposes!

Connection layout NW 5PS15 LD/PP .. .. KC0 JH				Pin Layout		Change No: C087330-07	
The reproduction, distribution and utilization of this document as well as the communication of its contents to others without express authorization is prohibited. Offenders will be held liable for the payment of damages. All rights reserved in the event of the grant of a patent, utility model or design. (ISO 16016)							
<b>HEIDENHAIN</b>		Serie	Version	Revision	Sheet	Page	
DR. JOHANNES HEIDENHAIN GmbH		<b>D730585</b>	<b>- 02</b>	<b>- A</b>	<b>- 01</b>	1/1	
83301 Traunreut, Germany		Document No					