



Biegeradius min. dauernd
 Min. bend radius for flexing --

Biegeradius min. einmalig
 Min. bend radius for rigid configuration 10mm

Schleppkettenradius min.
 Min. drag chain radius --

max. Kabellänge (L): siehe Techn. Daten des Gerätetyps
 For max. cable length (L): See Specifications of the encoder model

		IDnumber:
		C49798-05 [Fr.-Nr.] Phase: Serie
	Original drawing Scale	AGK JAE --> freies Ende (1H) Anschlussmaße
	Format	
Dimensions in mm	1:1	A3
		Tolerierung nach DIN ISO 8015 Tolerances as per DIN ISO 8015
		Allgemeintoleranzen ISO 2768-mH ±0.2mm: + 0.2 General tolerances ISO 2768-mH ±0.2mm: + 0.2
The reproduction, distribution and utilization of this document as well as the communication of its contents to others without express authorization is prohibited. Offenders will be held liable for the payment of damages. All rights reserved in the event of the grant of a patent, utility model or design. (ISO 16016)		
HEIDENHAIN DR. JOHANNES HEIDENHAIN GmbH 83301 Traunreut, Germany		Document number D 1063040-00-A-12
		1 of 1 Version Revision Sheet