



- [A] = Bearing.
- [M] = Measuring point for operating temperature.
- [H1] = e.g. 4x screw, M8x25mm, ISO 4762-8.8-MKL, Width A/F 6, Tightening torque 12 Nm, 4x washer ISO 7092-3-200HSV-A2
- [H2] = 1xCable gland, EN 62444, Width across flats 24mm, Tightening torque 9 ± 0.45 Nm, Cable Dia. 8 to 11mm
- [H3] = 4x screw, M5, ISO 4762-8.8, Width A/F 4, Tightening torque 3 ± 0.15 Nm,
- [H4] = Vibration measuring point.
- ↻ = Direction of shaft rotation for output signals as per the interface description.

09B	88B	7TK06
WELLA1	FLANA1	ANELA1

Original drawing		Scale		Format		ROD 1900		ID number:	
1/1		A2		Mating Dimensions		C183986-50		Serial production	
The reproduction, distribution and utilization of this document as well as the communication of its contents to others without express authorization is prohibited. Offenders will be held liable for the payment of damages. All rights reserved in the event of the grant of a patent, utility model or design. (ISO 16016)								Tolerances as per ISO 8015	
								General Tolerances ISO 2768:1989-mH ± 6 mm: ± 0.2	
HEIDENHAIN		Released		Version		Revision		Sheet	
								Page	
D1043373-02-A-01								1 of 1	
Document number									