



- (C) Biegeradius min. / min. bend radius 3mm
- Temperatursensor / Temperature sensor
- (B) Biegeradius min. / min. bend radius 3mm
- Durchmesser / Diameter 2,0mm
- Querschnitt / Cross section 0,16mm<sup>2</sup> / AWG26
- Biegeradius min. dauernd / Min. bend radius for flexing --
- (A) Biegeradius min. einmalig / Min. bend radius for rigid configuration 10mm

max. Kabellänge (L): siehe Techn. Daten des Gerätetyps  
 For max. cable length (L): See Specifications of the encoder model

			IDnumber:
			Change No. C182472-12 Phase: Serie
	Original drawing Scale   Format	AGK FCI --> Flange socket M12 (AES08)	
Dimensions in mm	1:1   A3	Anschlussmaße	
The reproduction, distribution and utilization of this document as well as the communication of its contents to others without express authorization is prohibited. Offenders will be held liable for the payment of damages. All rights reserved in the event of the grant of a patent, utility model or design. ( ISO 16016 )			Tolerances as per ISO 8015
			General Tolerances ISO 2768:1989-mH ±0,2
<b>HEIDENHAIN</b> DR. JOHANNES HEIDENHAIN GmbH 83301 Traunreut, Germany		Released 04.02.2026	Version   Revision   Sheet D 1063040-00-C -65 Document number
			1 of 1