



(B)	Temperatursensor / Temperature sensor	
	Biegeradius min. / min. bend radius	3mm
	Durchmesser / Diameter	2,0mm
	Querschnitt / Cross section	0,16mm <sup>2</sup> / AWG26

(A)	Biegeradius min. dauernd	--
	Min. bend radius for flexing	
	Biegeradius min. einmalig	10mm
	Min. bend radius for rigid configuration	

	Schleppkettenradius min.	--
	Min. drag chain radius	

max. Kabellänge (L): siehe Techn. Daten des Gerätetyps  
 For max. cable length (L): See Specifications of the encoder model

kundenseitige Anschlussmaße siehe D1140890 Bl.01 / D1218918 Bl.01  
 required mating dimensions see D1140890 Bl.01 / D1218918 Bl.01

Lochkreis-Durchmesser 32mm  
 bolt-hole circle diameter 32mm

			IDnumber:
			Change No. C056908-19 Phase: Serie
	Original drawing	AGK FCI --> Winkeldose SpeedTEC (1QSxx)	Tolerierung nach DIN ISO 8015 Tolerances as per DIN ISO 8015
Scale	Format	Anschlussmaße	Allgemeintoleranzen ISO 2768-mH $\pm 0,2$ General tolerances ISO 2768-mH $\pm 0,2$
Dimensions in mm	1:1	A3	
The reproduction, distribution and utilization of this document as well as the communication of its contents to others without express authorization is prohibited. Offenders will be held liable for the payment of damages. All rights reserved in the event of the grant of a patent, utility model or design. ( ISO 16016 )			
<b>HEIDENHAIN</b> DR.JOHANNES HEIDENHAIN GmbH 83301 Traunreut, Germany			Version   Revision   Sheet D 1063040-05-A-14 Document number
			1 of 1