



(B)	Temperatursensor / Temperature sensor	
	Biegeradius min. / min. bend radius	3mm
	Durchmesser / Diameter	2,0mm
	Querschnitt / Cross section	0,16mm ² / AWG26
	Biegeradius min. dauernd	--
	Min. bend radius for flexing	--
(A)	Biegeradius min. einmalig	
	Min. bend radius for rigid configuration	10mm
	Schleppkettenradius min.	--
	Min. drag chain radius	--

max. Kabellänge (L): siehe Techn. Daten des Gerätetyps
 For max. cable length (L): See Specifications of the encoder model

kundenseitige Anschlussmaße siehe D1140890 Bl.01 / D1218918 Bl.01
 required mating dimensions see D1140890 Bl.01 / D1218918 Bl.01

Lochkreis-Durchmesser 28mm
 bolt-hole circle diameter 28mm

		IDnumber:
		Change No. C056908-15
		Phase: Serie
	Original drawing	AGK FCI --> Winkeldose SpeedTEC (9ISxx)
Scale	Format	
Dimensions in mm	1:1	A3
		Anschlussmaße
		Tolerierung nach DIN ISO 8015 Tolerances as per DIN ISO 8015
		Allgemeintoleranzen ISO 2768-mH ±0.2mm; +0.2 General tolerances ISO 2768-mH ±0.2mm; +0.2
The reproduction, distribution and utilization of this document as well as the communication of its contents to others without express authorization is prohibited. Offenders will be held liable for the payment of damages. All rights reserved in the event of the grant of a patent, utility model or design. (ISO 16016)		
HEIDENHAIN DR. JOHANNES HEIDENHAIN GmbH 83301 Traunreut, Germany		Version Revision Sheet
		D 1063040-05-A-24
		Document number
		1 of 1