



Temperatursensor / Temperature sensor	
Biegeradius min. / min. bend radius	3mm
Durchmesser / Diameter	2,0mm
Querschnitt / Cross section	0,16mm <sup>2</sup> / AWG26

Biegeradius min. dauernd Min. bend radius for flexing	--
Biegeradius min. einmalig Min. bend radius for rigid configuration	10mm

Schleppkettenradius min.  
Min. drag chain radius

--

max. Kabellänge (L): siehe Techn. Daten des Gerätetyps  
For max. cable length (L): See Specifications of the encoder model

kundenseitige Anschlussmaße siehe D1140890 Bl.01 / D1218918 Bl.01  
required mating dimensions see D1140890 Bl.01 / D1218918 Bl.01

Lochkreis-Durchmesser 32mm  
bolt-hole circle diameter 32mm

			IDnumber:
			Change No. C056908-17 Phase: Serie
	Original drawing Scale   Format	AGK FCI --> Winkeldose SpeedTEC (9CSxx)	Tolerierung nach DIN ISO 8015 Tolerances as per DIN ISO 8015
Dimensions in mm	1:1   A3	Anschlussmaße	Allgemeintoleranzen ISO 2768-mH ±0,2mm; +0,2 General tolerances ISO 2768-mH ±0,2mm; +0,2
The reproduction, distribution and utilization of this document as well as the communication of its contents to others without express authorization is prohibited. Offenders will be held liable for the payment of damages. All rights reserved in the event of the grant of a patent, utility model or design. ( ISO 16016 )			
<b>HEIDENHAIN</b> DR. JOHANNES HEIDENHAIN GmbH 83301 Traunreut, Germany			Version   Revision   Sheet D 1063040-05-A-29 Document number
			1 of 1