





9J	Anschluss-Belegung
	Elektrischer Anschluss
	Geometrie Polbild (Steckseite)
JH	Firmenname
~1Vss	Ausgangssignal
..	Eingangssignal
..	Datenschnittstelle
..	Teilkreiszusatzspur
15 polig	Kundenseitige Steckerausführung
2+10	Versorgung 0V (Un)
4+12	Versorgung +V (Up)
Im Stecker	Versorgung verbunden mit Sensorleitung
Gehäuse	Außenschirm
1	Spannungssignal A+
9	Spannungssignal A-
3	Spannungssignal B+
11	Spannungssignal B-
14	Spannungssignal R+
7	Spannungssignal R-
15	Serielle Schnittstelle serial Data
13	Serielle Schnittstelle Takt
8	Zusätzliche Signale L1/ (Grenzlage)
6	Zusätzliche Signale L2/ (Grenzlage)
5	Freie Adern und Pins
0032	Ergänzungen

0032 = Grenzlagensignale L1, L2 (nur bei Längenmessgeräten) siehe technische Daten

9J	Pin configuration
	Electrical connection
	Geometry of pole pattern (plug side)
JH	company name
~1Vpp	Output signal
..	Input signal
..	Data interface
..	Additional circular scale track
15-pin	Customer's connection version
2+10	Supply 0V (Un)
4+12	Supply +V (Up)
in connector	Supply connected with sensor line
Housing	External shield
1	Voltage signal A+
9	Voltage signal A-
3	Voltage signal B+
11	Voltage signal B-
14	Voltage signal R+
7	Voltage signal R-
15	Serial interface for serial data
13	Serial interface for clock
8	Addit. signals L1/ (border position)
6	Addit. signals L2/ (border position)
5	Free wires and pins
0032	Additions

0032 = Limit position signals L1, L2 (only with linear encoders) see specifications

Connection layout 9J AQS15 ~1Vpp JH				Pin Layout		Change No: C184912-10	
The reproduction, distribution and utilization of this document as well as the communication of its contents to others without express authorization is prohibited. Offenders will be held liable for the payment of damages. All rights reserved in the event of the grant of a patent, utility model or design. (ISO 16016)							
HEIDENHAIN		Serie	Version	Revision	Sheet	Page	
DR. JOHANNES HEIDENHAIN GmbH		D1121221 - 01 - A - 04				1/1	
83301 Traunreut, Germany		Document No					