



XW	Anschluss-Belegung
	Elektr. Anschluss
	Geometrie Polbild (Steckseite)
..	Ausgangssignal
Taster	Eingangssignal
..	Datenschnittstelle
..	Teilkreiszusatzspur
15 polig	Kundenseitige Steckerausführung
8; 12	Versorgung 0V (Un)
6	Versorgung +5V (Up)
5	Versorgung +12V (Up)
Gehäuse	Außenschirm
4	Taster Signale Start
1	Taster Signale LED Anode
15	Taster Signale LED Kathode
7	Taster Signale Batteriewarnung invers
2	Taster Signale Bereitschaft 5V
3	Taster Signale Bereitschaft 12V
11	Taster Signale Trigger NC (normally close)
13	Taster Signale Trigger NC (normally close)
9; 10; 14	Freie Litzen und Pins

XW	Pin configuration
	Electrical connection
	Geometry of pole pattern
..	Output signal
Probe	Input signal
..	Data interface
..	Additional circular-scale track
15-pin	Customer's connection version
8; 12	Supply 0V (Un)
6	Supply +5V (Up)
5	Supply +12V (Up)
housing	External shield
4	Probe signals, start
1	Probe signals, LED Anode
15	Probe signals, LED Kathode
7	Probe signals, battery warning inverse
2	Probe signals, readiness 5V
3	Probe signals, readiness 12V
11	Probe signals, trigger NC (normally close)
13	Probe signals, trigger NC (normally close)
9; 10; 14	Free wires and pins

Connection layout XW 59B15 Probe ..		Pin Layout		Release No: C21656-25	
The reproduction, distribution and utilization of this document as well as the communication of its contents to others without express authorization is prohibited. Offenders will be held liable for the payment of damages. All rights reserved in the event of the grant of a patent, utility model or design.					
HEIDENHAIN DR. JOHANNES HEIDENHAIN GmbH 83301 Traunreut, Germany		Version	Revision	Sheet	Page
		D1089829 - 00 - A - 01			1/1
		Document No			