





<b>YG</b>	<b>Anschluss-Belegung</b>
	<b>Elektr. Anschluss</b>
	<b>Geometrie Polbild (Steckseite)</b>
<b>Taster</b>	<b>Ausgangssignal</b>
..	<b>Eingangssignal</b>
..	<b>Datenschnittstelle</b>
..	<b>Teilkreiszusatzspur</b>
15 polig	Kundenseitige Steckerausführung
12	Versorgung 0V (Un)
Gehäuse	Außenschirm
1	Taster Signale LED Anode
15	Taster Signale LED Kathode
11	Taster Signale Trigger NC (normally close)
1; 3; 4; 5; 6; 7;8; 9;10;13; 14	Freie Litzen und Pins

<b>YG</b>	<b>Pin configuration</b>
	<b>Electrical connection</b>
	<b>Geometry of pole pattern</b>
<b>Probe</b>	<b>Output signal</b>
..	<b>Input signal</b>
..	<b>Data interface</b>
..	<b>Additional circular-scale track</b>
15-pin	Customer's connection version
12	Supply 0V (Un)
housing	External shield
1	Probe signals, LED Anode
15	Probe signals, LED Kathode
11	Probe signals, trigger NC (normally close)
1; 3; 4; 5; 6; 7;8; 9;10;13; 14	Free wires and pins

Connection layout YG 16S15 Probe .. .. .				Pin Layout	Release No: N3552
The reproduction, distribution and utilization of this document as well as the communication of its contents to others without express authorization is prohibited. Offenders will be held liable for the payment of damages. All rights reserved in the event of the grant of a patent, utility model or design.					
<b>HEIDENHAIN</b> DR. JOHANNES HEIDENHAIN GmbH 83301 Traunreut, Germany				Version	Revision
				Sheet	Page
				<b>D1095999 - 00 - A - 01</b>	1/1
				Document No	