



<b>9J</b>	<b>Anschluss-Belegung</b> <b>Elektrischer Anschluss</b>
	
	<b>Geometrie Polbild (Steckseite)</b>
<b>JH</b>	<b>Firmenname</b>
<b>~1Vss</b>	<b>Ausgangssignal</b>
<b>..</b>	<b>Eingangssignal</b>
<b>..</b>	<b>Datenschnittstelle</b>
<b>..</b>	<b>Teilkreiszusatzspur</b>
<b>15 polig</b>	Kundenseitige Steckerausführung
<b>2+10</b>	Versorgung 0V (Un)
<b>4+12</b>	Versorgung +V (Up)
<b>Im Stecker</b>	Versorgung verbunden mit Sensorleitung
<b>Gehäuse</b>	Außenschirm
<b>1</b>	Spannungssignal A+
<b>9</b>	Spannungssignal A-
<b>3</b>	Spannungssignal B+
<b>11</b>	Spannungssignal B-
<b>14</b>	Spannungssignal R+
<b>7</b>	Spannungssignal R-
<b>15</b>	Serielle Datenübertragung serial Data
<b>13</b>	Serielle Datenübertragung Takt
<b>8</b>	Zusätzliche Signale L1/ (Grenzlage)
<b>6</b>	Zusätzliche Signale L2/ (Grenzlage)
<b>5</b>	Freie Adern und Pins
<b>0032</b>	Ergänzungen

0032 = Grenzlagensignale L1, L2 (nur bei Längenmessgeräten) siehe technische Daten

<b>9J</b>	<b>Pin configuration</b> <b>Electrical connection</b>
	
	<b>Geometry of pole pattern (plug side)</b>
<b>JH</b>	<b>company name</b>
<b>~1Vpp</b>	<b>Output signal</b>
<b>..</b>	<b>Input signal</b>
<b>..</b>	<b>Data interface</b>
<b>..</b>	<b>Additional circular scale track</b>
<b>15-pin</b>	Customer's connection version
<b>2+10</b>	Supply 0V (Un)
<b>4+12</b>	Supply +V (Up)
<b>in connector</b>	Supply connected with sensor line
<b>Housing</b>	External shield
<b>1</b>	Voltage signal A+
<b>9</b>	Voltage signal A-
<b>3</b>	Voltage signal B+
<b>11</b>	Voltage signal B-
<b>14</b>	Voltage signal R+
<b>7</b>	Voltage signal R-
<b>15</b>	Serial data transfer of serial data
<b>13</b>	Serial data transfer of clock pulse
<b>8</b>	Addit. signals L1/ (border position)
<b>6</b>	Addit. signals L2/ (border position)
<b>5</b>	Free wires and pins
<b>0032</b>	Additions

0032 = Limit position signals L1, L2 (only with linear encoders) see specifications

Connection layout 9J AIS15 ~1Vpp .. .. JH		Pin Layout		Release No: C184912-05	
The reproduction, distribution and utilization of this document as well as the communication of its contents to others without express authorization is prohibited. Offenders will be held liable for the payment of damages. All rights reserved in the event of the grant of a patent, utility model or design.					
<b>HEIDENHAIN</b> DR. JOHANNES HEIDENHAIN GmbH 83301 Traunreut, Germany		Version	Revision	Sheet	Page
		<b>D1121221 - 00 - A - 06</b>			1/1
Document No					