

Passmaß BASIC SIZE	Abmaße DEVIATIONS
∅ 17.3 H11	+0.110 0.000


Lochkreisdurchmesser 23.75mm
Bolt-hole circle diameter 23.75mm

Montagebohrung
Mounting hole

4x M2,5
Anzugsmoment 0,45 ±0,05 Nm
Torque 0,45 ±0,05 Nm

Mindestens 3,5mm tragende Gewindelänge
Load-bearing thread length at least 3,5mm

Sacklochbohrung oder Gewinde gedichtet
Blind hole or thread sealed



886 200 A4

			ID number:				
			Change No. C098663-30				
			Phase: Serie				
<p>Original drawing</p> <table border="1"> <tr> <td>Scale</td> <td>Format</td> </tr> <tr> <td>2:1</td> <td>A4</td> </tr> </table>			Scale	Format	2:1	A4	Tolerierung nach DIN ISO 8015 Tolerances as per DIN ISO 8015
			Scale	Format			
2:1	A4						
<p>Dimensions in mm</p>			Allgemeintol. ISO 2768-mH ≤6mm:±0,2 General tol. ISO 2768-mH ≤6mm:±0,2				

Montagebohrung LKD 23,75mm - M2,5
Flange socket

Anschlussmaße / Mating Dimensions

The reproduction, distribution and utilization of this document as well as the communication of its contents to others without express authorization is prohibited. Offenders will be held liable for the payment of damages. All rights reserved in the event of the grant of a patent, utility model or design. (ISO 16016)

HEIDENHAIN
DR. JOHANNES HEIDENHAIN GmbH
83301 Traunreut, Germany

Version	Revision	Sheet	Page
D1140890-00 - A-03			1 of 1
Document number			