



| | | |
|---|--|-------------------|
| J9 | Anschluss-Belegung | |
|  | Elektrischer Anschluss | |
| .. | Geometrie Polbild (Steckseite) | |
| JH | Firmenname | JH |
| TTL | Ausgangssignal | TTL |
| .. | Eingangssignal | .. |
| .. | Datenschnittstelle | .. |
| .. | Teilkreiszusatzspur | .. |
| 10 polig | Kundenseitige Steckerausführung | Ader |
| 2 | Versorgung 0V (Un) | weißgrün und weiß |
| 1 | Versorgung +V (Up) | braungrün+blau |
| Im Stecker | Versorgung verbunden mit Sensorleitung | Im Stecker |
| Gehäuse | Außenschirm | Schirm |
| 7 | Rechteck-Signal Ua1 | braun |
| 8 | Rechteck-Signal Ua1 invers | grün |
| 5 | Rechteck-Signal Ua2 | grau |
| 6 | Rechteck-Signal Ua2 invers | rosa |
| 9 | Rechteck-Signal Ua0 | rot |
| 10 | Rechteck-Signal Ua0 invers | schwarz |
| 3;4 | Freie Adern und Pins | |
| | Freie Adern und Pins | gelb |
| | Freie Adern und Pins | violett |

| | | |
|---|---|------------------------|
| J9 | Pin configuration | |
|  | Electrical connection | |
| .. | Geometry of pole pattern (plug side) | |
| JH | company name | JH |
| TTL | Output signal | TTL |
| .. | Input signal | .. |
| .. | Data interface | .. |
| .. | Additional circular scale track | .. |
| 10-pin | Customer's connection version | Wire |
| 2 | Supply 0V (Un) | white, green and white |
| 1 | Supply +V (Up) | brown, green and blue |
| in connector | Supply connected with sensor line | in connector |
| Housing | External shield | Shield |
| 7 | Square-wave signal Ua1 | brown |
| 8 | Square-wave signal Ua1 inverse | green |
| 5 | Square-wave signal Ua2 | grey |
| 6 | Square-wave signal Ua2 inverse | pink |
| 9 | Square-wave signal Ua0 | red |
| 10 | Square-wave signal Ua0 inverse | black |
| 3;4 | Free wires and pins | |
| | Free wires and pins | yellow |
| | Free wires and pins | violet |

| | | | |
|--|------------|----------------|------------|
| Connection layout J9 DIB10 TTL JH | Pin Layout | Change No: C03 | C038102-05 |
|--|------------|----------------|------------|

The reproduction, distribution and utilization of this document as well as the communication of its contents to others without express authorization is prohibited.